

Cable management



Cable route

for TS

- For cable clamping and routing with network and server applications
- Mounting across the entire depth with 800 mm width, mounting only behind the second 482.6 mm (19") pair of mounting angles with 600 mm width
- Toolless fast assembly
- Alternatively suitable for screw-fastening
- Multi-functional punchings for cable management accessories

Material:

- Sheet steel

Colour:

- RAL 9005

Height mm	Packs of	Model No.
2000 – 2200	1 pc(s).	5502.120

+ Accessories:

- Cable ties, see page 667
- Nylon loop tape, see page 667
- Shunting rings, see page 670
- Cable routing bars, see page 673



Surplus cable holder

For fastening at the rear area of the enclosure, or at the side of network enclosures. The surplus cable holder can be attached to all depth stays or to punched sections and rails with a 25 mm pitch pattern – mounting dimension 150 mm. May also be joined together.

Material:

- Sheet steel

Colour:

- RAL 7035

W x H x D mm	Packs of	Model No.
280 x 151 x 75	1 pc(s).	7220.500