



## System accessories Page 507

Compact 482.6 mm (19") enclosure for small networks.

### Benefits:

- May be used as wall-mounted, under-desk or desktop enclosure
- Free access from three sides for interior installation
- Passive ventilation with vent slots
- Rear panel prepared to accommodate a fan
- Freely selectable door hinging

### Material:

- Sheet steel
- Viewing window: Single-pane safety glass, 3 mm

### Surface finish:

- Powder-coated

### Colour:

- RAL 7035

### Supply includes:

- Enclosure with glazed door
- Side panels (1 x fixed, 1 x slot-in) with vent slots
- Knockouts for cable entry via roof or base
- Slot-in rear panel with knockouts for cable entry and fan accommodation
- 482.6 mm (19") mounting level, 5 U, horizontal front and rear, depth-variable, distance between levels 434 – 489 mm
- Security lock 12321 on the door, side and rear panel
- 4 plastic feet, self-adhesive

### Technical details:

Available on the Internet

<b>Units U</b>	Packs of	5	Page
<b>Width mm</b>		300	
<b>Height mm</b>		540	
<b>Depth mm</b>		600	
<b>Model No.</b>	1 pc(s).	<b>7501.000</b>	
<b>Accessories</b>			
Brush strip	1 pc(s).	7072.200	657
Wall mounting bracket		see page	587
Fan expansion kit	1 set(s)	7980.100	438
Socket strips	1 pc(s).	7240.220	422
Blanking panel, 482.6 mm (19")	2 pc(s).	7151.035	696
Cable management panel		see page	674
Cable entry panel		see page	677