

Accessories



Component shelf, static installation

for 482.6 mm (19") system punchings, depth-variable for TS IT, TE

Applications:

- Depth-variable to adapt to individual distances between levels

Benefits:

- Tool-free, time-saving one-man assembly

Installation options:

- 482.6 mm (19") L mounting angles, front and rear
- 482.6 mm (19") mounting frames front and rear

Material:

- Sheet steel

Surface finish:

- Spray-finished

Colour:

- RAL 9005

Supply includes:

- Assembly parts

Distance between levels mm	Load capacity (static)	Height U	Packs of	Model No.
400 - 600	100 kg	1	1 pc(s).	5501.695
600 - 900	100 kg	1	1 pc(s).	5501.705
400 - 600	50 kg	0.5	1 pc(s).	5501.655
600 - 900	50 kg	0.5	1 pc(s).	5501.665



Component shelf, complete set, pull-out

482.6 mm (19") system punchings

The complete set contains a vented component shelf, telescopic slides and a mounting kit for direct attachment. The mounting kit also offers depth-variable attachment within 395 – 645 mm on a 25 mm pitch pattern.

Installation options:

- 482.6 mm (19") L mounting angles, front and rear
- 482.6 mm (19") mounting frames front and rear

Material:

- Base: Sheet steel

Surface finish:

- Base: Spray-finished
- Mounting kit/telescopic slides: Zinc-plated

Colour:

- RAL 7035

Supply includes:

- 1 component shelf, telescopic slides, mounting kit

Width mm	482.6
Depth mm	500
Distance between levels mm	395 - 645
Load capacity (static)	50 kg area load
Packs of	1 pc(s).
Model No.	7000.625



Cable route

for TE

For vertical cable entry at the side of the 482.6 mm (19") mounting frame for TE, independently from the enclosure frame.

Material:

- Sheet steel

Surface finish:

- Zinc-plated

Supply includes:

- Assembly parts

Width mm	Height mm	Packs of	Model No.
100	1700	1 pc(s).	7000.685