

# System accessories AX

## Viewing window/operating panel

### Viewing window

For mounting on

- AX enclosures instead of the door
- Surfaces

Max. installation depth: (depth -4 mm)

Visible area: (width -60 mm) x (height -60 mm)

#### Material:

- Frame: Aluminium, natural anodised
- Glazed panel: Acrylic

#### Protection category IP to IEC 60 529:

- IP 54

#### Supply includes:

- Plastic handle with lock insert no. 3524 E

#### Depth 36 mm

For use as door variant with	Width mm	Height mm	Model No.
1050.000, 1350.000, 1007.000	497	497	<b>2733.010</b>
1039.000, 1339.000, 1009.000	597	377	<b>2730.010</b>
1010.000, 1054.000, 1060.000, 1360.000	597	597	<b>2731.010</b>
1012.000, 1076.000, 1376.000	597	757	<b>2732.010</b>

#### Depth 62 mm

For use as door variant with	Width mm	Height mm	Model No.
1050.000, 1350.000, 1007.000	497	497	<b>2763.010</b>
1039.000, 1339.000, 1009.000	597	377	<b>2760.010</b>
1010.000, 1054.000, 1060.000, 1360.000	597	597	<b>2761.010</b>
1012.000, 1076.000, 1376.000	597	757	<b>2762.010</b>



### Operating panel

For mounting on

- AX enclosures instead of the door
- Surfaces

Frame construction with a 3 mm aluminium plate secured from the inside.

#### Material:

- Aluminium, natural anodised

#### Protection category IP to IEC 60 529:

- IP 54

#### Supply includes:

- Aluminium frame
- Display panel
- Hinges
- Brackets

For use as door variant for AX	Width mm	Height mm	Depth mm	Model No.
1004.000 1011.000 1031.000	377	297	36	<b>2741.010</b>
1006.000 1303.000 1380.000	377	377	36	<b>2742.010</b>
1008.000 1038.000 1338.000	377	597	36	<b>2743.010</b>
1007.000 1013.000 1050.000 1350.000	497	497	36	<b>2745.010</b>
1009.000 1039.000 1339.000	597	377	36	<b>2744.010</b>
1010.000 1060.000 1304.000 1360.000	597	597	36	<b>2746.010</b>

Area available for population:  
(width -70 mm) x (height -70 mm)

Dimensions of aluminium plate:  
(width -54 mm) x (height -54 mm)



#### Accessories:

- Cam lock 2749.100, see page 65



### Cam lock

#### for operating panel

May be retrofitted to the operating area or enclosure wall of operating panels.

Standard double-bit insert may be exchanged for lock inserts, type C.

Packs of	Model No.
1 pc(s).	<b>2749.100</b>



#### Accessories:

- Lock inserts, type C, see Catalogue 35, page 680

