

# 482.6 mm (19") installation

## Installation kits for mounting angles



### Mounting angles additional fastening attachment

#### for 800 mm wide TS network enclosures

The additional fastening attachment counteracts bending of the mounting angles mounted on installation brackets in case of unevenly distributed loads. It is attached directly to 482.6 mm (19") mounting angles and to the punched section with mounting flange fitted in the depth (inner mounting level).

**Material:**  
Sheet steel, zinc-plated, passivated

**Supply includes:**  
Assembly parts.



Packs of	Model No. DK
2	7284.135

**! Also required:**

TS punched section with mounting flange for the inner mounting level, see page 993 – 995.



### TS punched section with mounting flange as installation kit

for

- Mounting angles, 482.6 mm (19")
- Mounting angles, metric, Mounting dimension 465 mm


#### Installation in enclosure width 600 mm

The installation kit consists of 4 TS punched sections with mounting flange 17 x 73 mm to accommodate mounting angles. One pack is sufficient for installing one or two 482.6 mm (19") attachment levels. For exceptionally heavy installed equipment, we recommend the installation of additional punched sections.

For enclosures		Packs of	Model No. TS
Width mm	Depth mm		
600	600	4	8612.060
600	800	4	8612.080
600	900	4	8612.090
600	1000	4	8612.000
600	1200	4	8612.020

**Material:**  
Sheet steel, zinc-plated, passivated

**Supply includes:**  
Assembly parts.



### Depth stays as installation kit for mounting angles, 482.6 mm (19")

#### Installation in enclosure width 800 mm

One installation kit consists of 4 depth stays to accommodate mounting angles. One pack is sufficient for installing one or two 482.6 mm (19") attachment levels. For exceptionally heavy installed equipment, we recommend the installation of an additional depth stay in the centre. The front cut-out makes cable routing easier with full configuration

**Material:**  
Sheet steel, zinc-plated, passivated

**Supply includes:**  
Assembly parts.

For enclosures		Packs of	Model No. DK
Width mm	Depth mm		
800	600	4	7827.600
800	800	4	7827.800
800	900	4	7827.900
800	1000	4	7827.000

**↔ Possible alternative:**

Depth stays TS for mounting angles, see page 1096.

