

Support arm system CP 40, steel

	Rotating/tilting	Fixed	Length mm	Weight kg	Colour RAL	Enclosure section	Desk section	Wall section
						Model No.		
Tilting adaptor +100/-60° for support arm connection □ 120 x 65 mm/□ 90 x 71 mm								
 see page 162	■	-	-	0.8	7035/ 7024	6206.460	-	-
Attachment CP 40, steel, for support arm connection □ 90 x 71 mm								
	-	■	-	1.0	7024	6501.070	-	-
Coupling CP 40, steel, for support arm connection □ 90 x 71 mm								
	■	-	-	1.1	7024	6501.050	-	-
Coupling CP 40, steel, for support arm connection □ 120 x 65 mm								
	■	-	-	1.5	7024	6501.130	-	-
Connection console VESA 75/100 for support arm connection □ 120 x 65 mm								
 see page 156	-	■	-	1.1	7035/ 7024	6206.480	-	-
Angle coupling 90° CP 40, steel, for support arm connection □ 90 x 71 mm								
	■	-	-	1.6	7024	6501.120	-	-
Support section CP 40, steel								
	-	-	500 1000	2.1 4.2	7035 7035		6501.000 6501.020	
Angle piece 90° CP 40, steel								
	-	■	-	1.1	7024	6501.140	-	6501.140
Top-mounted joint CP 40, steel								
	■	-	-	1.8	7024	-	-	6501.160
Wall-mounted hinge CP 40, steel								
	■	-	-	2.2	7024	-	-	6501.150
Wall/base mounting bracket, CP 40, steel								
	-	■	-	0.7	7024	-	-	6501.110
Mounting component CP 40, steel, for signal pillar								
 see page 720	-	■	-	0.3	7024	2375.030	-	-
Accessories								
Angle adaptor 90° for support arm combination CP 60/40 6206.640								see page 158