

# Doors/locks

## Lock systems



### Cam locks

	With double-bit insert	With lock cylinder insert <sup>3)</sup>	With double-bit insert,	With lock cylinder insert <sup>3)</sup>	With lock insert, lock E1 <sup>1)</sup> RAL 7035	With double-bit insert
Material: Enclosure	Die-cast zinc, nickel-plated		Fibreglass-reinforced polyamide			Made entirely from stainless steel 1.4404 (AISI 316L)
	<b>Model No.</b>					
	<b>2520.000</b>	<b>2530.000</b>	<b>2420.000</b>	<b>2430.000</b>	<b>2540.500</b>	<b>2304.000</b>

<b>Lock inserts</b>						
7 mm square	2523.000	-	2460.000	-	-	-
8 mm square	2526.000	-	2461.000	-	-	-
7 mm triangular	2527.000	-	2462.000	-	-	-
8 mm triangular	2528.000	-	2463.000	-	-	-
Screwdriver	-	-	2464.000	-	-	-
Daimler insert	2522.000	-	2465.000	-	-	-
3 mm double-bit	2483.000	-	2466.000	-	-	-
Fiat	-	-	2307.000	-	-	-
6.5 mm triangular (CNOMO)	-	-	2460.650	-	-	-
<b>Lock cylinder inserts</b>						
With lock no. 3524 E <sup>2)</sup>	-	-	2571.000	-	-	-

<sup>1)</sup> Only for use with VW, Audi, SEAT, SkodaAuto, supplied without key

<sup>2)</sup> With two keys

<sup>3)</sup> Lock no. 3524 E



### Lock inserts

Version	A	C	D	E	F
Material	Die-cast zinc	Die-cast zinc	Die-cast zinc	Plastic	Die-cast zinc
Length	27 mm	41 mm	47 mm		
	<b>Model No.</b>				
7 mm square	<b>2460.000</b>	<b>2523.000</b>	-	-	<b>8611.100</b>
8 mm square	<b>2461.000</b>	<b>2526.000</b>	-	<b>1488.000</b>	<b>8611.110</b>
7 mm triangular	<b>2462.000</b>	<b>2527.000</b>	-	-	<b>8611.120</b>
8 mm triangular	<b>2463.000</b>	<b>2528.000</b>	-	<b>1486.000</b>	<b>8611.130</b>
Screwdriver	<b>2464.000</b>	-	-	-	<b>8611.140</b>
Daimler insert	<b>2465.000</b>	<b>2522.000</b>	-	-	<b>8611.150</b>
3 mm double-bit	<b>2466.000</b>	<b>2483.000</b>	<b>2484.000</b>	<b>1492.000</b>	<b>8611.160</b>
Fiat	<b>2307.000</b>	-	-	-	<b>8611.170</b>
6.5 mm triangular (CNOMO)	<b>2460.650</b>	-	-	-	<b>8611.220</b>