

Roof/wall mounting

Roof



Spacers

for roof plate TS

To raise the TS roof for ventilation purposes, in three different heights.

Not suitable for crane transportation!

Thread: M12

Material:

– Hexagonal sectional steel

Surface finish:

– Zinc-plated

Supply includes:

– Assembly parts

Height mm	Packs of	Model No.
10	4 pc(s).	2422.000
20	4 pc(s).	2423.000
50	4 pc(s).	7967.000



Eyebolts

for TS, SE

For crane transportation of enclosures, where not already included in the supply.

Thread: M12

Supply includes:

– 4 eyebolts M12
– 4 serrated lock washers A 12.5

Material	Packs of	Model No.
Sheet steel, zinc-plated Cl 5	4 pc(s).	4568.000
Stainless steel 1.4301 (AISI 304)	4 pc(s).	4568.500



Eyebolts

for CM

For crane transportation of enclosures, with reinforcement plate to be inserted underneath.

Mounting via the two holes in the top of the CM.

Thread: M12

Supply includes:

– Eyebolts
– Reinforcement plates

Packs of	Model No.
2 pc(s).	2509.500



Eyebolts

for AE

For crane transportation of enclosures, with reinforcement plate to be inserted underneath.

Thread: M12

Supply includes:

– Eyebolts
– Reinforcement plates

Packs of	Model No.
4 pc(s).	2509.000