

Front assembly

Mounting kit

for Optipanel

For installation of

- Aluminium front panels
- Command panels
- Keyboards

for drilled holes

Supply includes:

- Packs of 30 retaining claws, captive nuts, screws and sealing washers

for threaded bolts

Supply includes:

- Packs of 10 retaining claws and cap screws

for screw clamp

Supply includes:

- Packs of 4 pressure plates, 4 attachment strips

Note:

- The command panels MP 377 12" Touch, MP 377 15" Touch are installed using an adaptor plate

For front panels	Thread	Model No.
Others	M4	6058.000
Rittal and others	M5	6053.000

For front panels	Thread	Model No.
Others	M4	6058.500
Rittal and others	M5	6053.500 ¹⁾

¹⁾ For the installation of TFT monitors 15", 17" and 19"

For direct installation of	Model No.
Siemens Sinumerik: OP 010, OP 010C, OP 012, OP 015, OP 019, MCP 483, PP 012, Querty 19", KB 483C, TP 015A	6053.210
Siemens Simatic: Panel PC 477C, 577C, 677C: 12.1" Touch, 15.1" Touch, 12.1" Key, 15.1" Key, 19" Touch ¹⁾ , 22" Touch ¹⁾ , Flat Panel ¹⁾ 12", 15", 19"	
Industrial Flat Panel: IFP 1200 Touch, IFP 1500 Touch, IFP 1200 Key, IFP 1500 Key, IFP 1900 Touch, IFP 2200 Touch	
Industrial Thin Client: ITC 1200, ITC 1500, ITC 1900, ITC 2200	

The mounting set can only be installed vertically

¹⁾ 2 packs are required

Mounting kit

for Comfort Panel

For the installation of aluminium front panels, command panels and keyboards.

Supply includes:

- 6058.800, 6053.800:
20 each of retaining claws, captive nuts, screws, nuts and sealing washers
- 6053.300:
8 medium retaining claws, 8 short retaining claws, 4 long retaining claws

1) 6058.800, 6053.800

2) 6053.300

For drilled holes/bolts/front panel mounting from the rear

Thread	Model No.
M4	6058.800
M5	6053.800

For screw clamp

For installation of	Model No.
Siemens Sinumerik: OP 010, OP 010 C, OP 012, OP 015, OP 015 A, OP 019, MCP 483 C, MCP 483, PP 012, PP 012 extension, MCP, KB 483 C, Querty 19"	6053.300
Siemens Simatic: TP 900 Comfort, KP 900 Comfort, TP 1200 Comfort, KP 1200 Comfort, KTP 1000 Basic, KTP 1500 Basic	
Panel PC 477C, 577C, 677C: 12.1" Key, 12.1" Touch, 15.1" Key, 15.1" Touch, 19" Touch, 22" Touch ¹⁾	
MP 377 12" Touch, MP 377 15" Touch, MP 377 19" Touch	
Industrial Flat Panel: IFP 1200 Touch, IFP 1500 Touch, IFP 1200 Key, IFP 1500 Key, IFP 1900 Touch, IFP 2200 Touch	
Industrial Thin Client: ITC 1200, ITC 1500, ITC 1900, ITC 2200	
B & R: Automation Panel, Panel PC	

¹⁾ 2 packs are required

