

Baying systems TS 8



System accessories Page 507 **Installation accessories for TS modular front design** Page 552 **Compartment configuration** Page 283

Material and surface finish:

- Enclosure frame: Sheet steel, 1.5 mm, dipcoat-primed
- Rear panel: Sheet steel, 1.5 mm, dipcoat-primed, powder-coated on the outside, textured paint
- Gland plates: Sheet steel, 1.5 mm, zinc-plated

Colour:

- RAL 7035

Basis of test:

- IEC 61 439-1/-2
- IEC 61 641

Protection category IP to

IEC 60 529:

- Up to IP 54, depending on the panels

Supply includes:

- Enclosure frame
- Rear panel
- Three-piece gland plates

Technical details:

Available on the Internet

Modular enclosures, height 2000 mm

Width mm	Packs of	400	600	800	400	600	800	Page
Height mm		2000	2000	2000	2000	2000	2000	
Depth mm		600	600	600	800	800	800	
Model No.	1 pc(s).	9670.406	9670.606	9670.806	9670.408	9670.608	9670.808	
Weight kg		43.8	51.0	61.0	46.0	53.7	64.2	
Accessories								
Side panels, screw-fastened, sheet steel	2 pc(s).	8106.235	8106.235	8106.235	8108.235	8108.235	8108.235	534
Flex-Block corner pieces, 100 mm	1 set(s)	8100.000	8100.000	8100.000	8100.000	8100.000	8100.000	511
Flex-Block trim panels, 100 mm, sealed, for width	1 set(s)	8100.400	8100.600	8100.800	8100.400	8100.600	8100.800	511
Flex-Block trim panels, 100 mm, sealed, for depth	1 set(s)	8100.600	8100.600	8100.600	8100.800	8100.800	8100.800	511
Flex-Block corner pieces, 200 mm	1 set(s)	8200.000	8200.000	8200.000	8200.000	8200.000	8200.000	511
Flex-Block trim panels, 200 mm, sealed, for width	1 set(s)	8200.400	8200.600	8200.800	8200.400	8200.600	8200.800	511
Flex-Block trim panels, 200 mm, sealed, for depth	1 set(s)	8200.600	8200.600	8200.600	8200.800	8200.800	8200.800	511
Base/plinth components, front and rear, 100 mm	1 set(s)	8601.400	8601.600	8601.800	8601.400	8601.600	8601.800	513
Base/plinth trim panels, side, 100 mm	1 set(s)	8601.060	8601.060	8601.060	8601.080	8601.080	8601.080	514
Base/plinth components, front and rear, 200 mm	1 set(s)	8602.400	8602.600	8602.800	8602.400	8602.600	8602.800	513
Base/plinth trim panels, side, 200 mm	1 set(s)	8602.060	8602.060	8602.060	8602.080	8602.080	8602.080	514
Levelling feet	4 pc(s).	4612.000	4612.000	4612.000	4612.000	4612.000	4612.000	520
Angular baying bracket	4 pc(s).	8800.430	8800.430	8800.430	8800.430	8800.430	8800.430	545
Baying connector, external	6 pc(s).	8800.490	8800.490	8800.490	8800.490	8800.490	8800.490	544
Roof plates		see page	see page	see page	see page	see page	see page	583
Partial doors		see page	see page	see page	see page	see page	see page	552
Front trim panels, top		see page	see page	see page	see page	see page	see page	553
Front trim panels, bottom		see page	see page	see page	see page	see page	see page	553