

Baying systems TS 8



System accessories Page 507 Compartment configuration Page 283

Material and surface finish:

- Enclosure frame: Sheet steel, 1.5 mm, dipcoat-primed
- Roof: Sheet steel, 1.5 mm, dipcoat-primed, powder-coated on the outside, textured paint
- Door: Sheet steel, 2 mm, dipcoat-primed, powder-coated on the outside, textured paint
- Rear panel: Sheet steel, 1.5 mm, dipcoat-primed, powder-coated on the outside, textured paint
- Gland plates: Sheet steel, 1.5 mm, zinc-plated
- Punched section without mounting flange: Sheet steel, zinc-plated

Colour:

- RAL 7035

Basis of test:

- IEC 61 439-1/-2
- IEC 61 641

Protection category IP to IEC 60 529:

- Up to IP 3X, depending on the panels

Supply includes:

- Enclosure frame with r/h door hinge, left side open
- Roof
- Rear panel
- Three-piece gland plates
- Punched sections without mounting flanges 23 x 73 mm for enclosure height
- Lock: 3 mm double-bit

Technical details:

Available on the Internet

Fuse-switch-disconnector enclosures

Width mm	Packs of	1000	1200	1200	Page
Height mm		2000	2000	2000	
Depth mm		600	600	800	
Model No.	1 pc(s).	9670.006	9670.106	9670.108	
Weight kg		97.0	116.0	123.0	
Accessories					
Side panels, screw-fastened, sheet steel	2 pc(s).	8106.235	8106.235	8108.235	534
Flex-Block corner pieces, 100 mm	1 set(s)	8100.000	8100.000	8100.000	511
Flex-Block trim panels, 100 mm, sealed, for width	1 set(s)	8100.010	8100.120	8100.120	511
Flex-Block trim panels, 100 mm, sealed, for depth	1 set(s)	8100.600	8100.600	8100.800	511
Flex-Block corner pieces, 200 mm	1 set(s)	8200.000	8200.000	8200.000	511
Flex-Block trim panels, 200 mm, sealed, for width	1 set(s)	8200.010	8200.120	8200.120	511
Flex-Block trim panels, 200 mm, sealed, for depth	1 set(s)	8200.600	8200.600	8200.800	511
Base/plinth components, front and rear, 100 mm	1 set(s)	8601.000	8601.200	8601.200	513
Base/plinth trim panels, side, 100 mm	1 set(s)	8601.060	8601.060	8601.080	514
Base/plinth components, front and rear, 200 mm	1 set(s)	8602.000	8602.200	8602.200	513
Base/plinth trim panels, side, 200 mm	1 set(s)	8602.060	8602.060	8602.080	514
Levelling feet	4 pc(s).	4612.000	4612.000	4612.000	520
Angular baying bracket	4 pc(s).	8800.430	8800.430	8800.430	545
Baying connector, external	6 pc(s).	8800.490	8800.490	8800.490	544
Front trim panels	1 set(s)	9674.340	9674.340	9674.340	290
Contact hazard protection cover plate	1 set(s)	9674.362	9674.366	-	291
Divider panel	1 pc(s).	9674.306	9674.306	9674.308	291
Roof plates	1 pc(s).	9660.255	9660.265	9659.555	583