

# RiLine accessories

## Connection system

### Connection block

**Material:**

**Chassis**

- Polyamide (PA 6.6).
- Fire protection corresponding to UL 94-V0

**Cover**

- ABS
- Fire protection corresponding to UL 94-V0

**Colour:**

RAL 7035

**Supply includes:**

3 terminals including cover.

**Note:**

When using the terminal on 2-pole busbar systems (SV 9340.040), the terminal must be rotated through 180° for connection to the PE busbar.

**Technical information:**

Available on the Internet.

**Detailed drawings:**

Available on the Internet.



Outlet	Packs of	top/bottom	top/bottom	Page
Connection of round conductors mm <sup>2</sup> ● fine-wire with wire end ferrule ● multi-wire		95 – 185 95 – 300	– –	
Clamping area for laminated copper bars W x H mm ● For 5 mm bar thickness ● For 10 mm bar thickness		33 x 27 33 x 22	65 x 27 65 x 22	
Width mm		50	85	
Height mm		88	88	
For bar thickness mm		5/10	5/10	
<b>Model No. SV</b>	3	<b>9342.311</b>	<b>9342.321</b>	
<b>Accessories</b>				
Laminated copper bars		■	■	314