





Rated current max. 65 A, with tension spring clamp

						
Rated current max. A	Packs of	65	65	65	65	Page
Rated operating voltage V, ~		690, 3~	690, 3~	690, 3~	690, 3~	
Number of poles		3-pole	3-pole	3-pole	3-pole	
Connection of round conductors mm ²		2.5 - 16	2.5 - 16	2.5 - 16	2.5 - 16	
With support frame mm		–	–	55 x 170	55 x 237	
With support frame support		–	–	–	■	
With PinBlock		–	–	–	–	
Support rails Qty/height mm		1 / 10	2 / 10	1 / 10	2 / 10	
Support rail version		TS 55E	TS 55E TS 55D	TS 55E	TS 55E TS 55D-V	
Width mm		55	55	55	55	
Height mm		208	208	208	272	
For bar systems with centre-to-centre spacing mm		60	60	60	60	
For bar thickness mm		5/10	5/10	5/10	5/10	
Model No.	1 pc(s).	9340.610	9340.620	9340.630	9340.650	
Accessories						
Cable set		see page	see page	see page	see page	260
Twin cords		see page	see page	see page	see page	260
Connection pin	20 pc(s).	9340.280	9340.280	9340.280	9340.280	260
Insert strip	2 pc(s).	9340.290	9340.290	9340.290	9340.290	259
Support rails		from page	from page	from page	from page	259
OM supports		see page	see page	see page	see page	225
PinBlock	5 pc(s).	–	–	9342.810	9342.810	260

Accessories



Therm software

see page 385