

NH slimline fuse-switch disconnectors, sizes 00 to 3

Size 00 – 1, design 3-pole, switchable

Size	Packs of	00	00	1	Page
Twin track		–	–	–	
Rated operating current max. A		160	160	250	
Rated operating voltage V, ~		690, 3~	690, 3~	690, 3~	
Number of poles		3-pole	3-pole	3-pole	
Cable outlet		Top/bottom	Top/bottom	Top/bottom	
Type of connection		Screw M8	Box terminal	Bolt M12	
Connection of round conductors mm ²		1.5 - 95	1.5 - 95	6 - 240	
Width mm		50	50	100	
Height mm		670	670	670	
For converter installation		■	■	■	
For bar systems with centre-to-centre spacing mm		185	185	185	
For bar thickness mm		10	10	10	
Note on Model No.		–	–	–	
Model No.	1 pc(s).	9677.000	9677.025	9677.100	

Accessories

Connection space cover	1 pc(s).	see page	see page	9677.410	111
Contact terminal	3 pc(s).	9677.450	9677.450	9677.460	112
Busbar terminal	3 pc(s).	9677.470	9677.470	9677.480	112
Prism terminal	3 pc(s).	9677.420	–	–	112
V connection terminal	3 pc(s).	–	–	9677.430	113
Micro-switch	5 pc(s).	3071.000	3071.000	3071.000	Cat. 34, 263
Current converter	1 pc(s).	9677.810	9677.810	see page	113
Cover	5 pc(s).	–	–	9677.415	114

Size 2 – 3, design 3-pole, switchable

Size	Packs of	2	3	3	Page
Twin track		–	–	■	
Rated operating current max. A		400	630	1250	
Rated operating voltage V, ~		690, 3~	690, 3~	690, 3~	
Number of poles		3-pole	3-pole	3-pole	
Cable outlet		Top/bottom	Top/bottom	Top/bottom	
Type of connection		Bolt M12	Bolt M12	Bolt M12	
Connection of round conductors mm ²		6 - 240	6 - 240	6 - 240	
Width mm		100	100	200	
Height mm		670	670	670	
For converter installation		■	■	■	
For bar systems with centre-to-centre spacing mm		185	185	185	
For bar thickness mm		10	10	10	
Note on Model No.		–	–	Special design	
Model No.	1 pc(s).	9677.200	9677.300	9677.340	

Accessories

Connection space cover	1 pc(s).	9677.410	9677.410	9677.410	111
Contact terminal	3 pc(s).	9677.460	9677.460	9677.460	112
Busbar terminal	3 pc(s).	9677.480	9677.480	9677.480	112
Prism terminal		–	–	–	112
V connection terminal	3 pc(s).	9677.430	9677.440	9677.440	113
Micro-switch	5 pc(s).	3071.000	3071.000	3071.000	Cat. 34, 263
Current converter		see page	see page	see page	113
Cover	5 pc(s).	9677.415	9677.415	9677.415	114