

Air/water heat exchangers

Roof-mounted, useful cooling output 2000 W, water-carrying parts CuAL

Model No. SK	3373.500	3373.100	Page
Thermostat (factory setting +35°C)	e-Comfort controller ■	–	
	Basic controller –	■	
Useful cooling output	L 35 W 10, 400 l/h	2000 W	
Rated operating voltage V, Hz	230, 1~, 50/60		
Dimensions mm	W x H x D 400 x 950 x 140		

Rated current max.	0.38 A/0.43 A
Pre-fuse T	4.0 A
Cooling medium	Water (for specifications see Internet; user manual)
Water inlet temperature	+1°C to +30°C
Water connection	Quick-release fastener system
Permissible operating pressure p. max.	1 to 10 bar
Operating temperature and setting range	+1°C to +70°C
Protection category to IEC 60 529	IP 55 ¹⁾
Duty cycle	100%
Type of connection	Plug-in terminal strip
Weight	20 kg
Air throughput of fan (unimpeded air flow)	600/625 m ³ /h

Accessories	Packs of			
Door-operated switch	1	4127.010	4127.010	684
SK BUS system	1	3124.100	–	477
Interface board	1	3124.200	–	477
Condensate hose	1	3301.612	3301.612	485
Threaded adaptor for quick-release fastener with G3/8" internal thread	2	3201.900	3201.900	486
Threaded adaptor for quick-release fastener with G3/8" external thread	2	3201.910	3201.910	486
Flow regulator valve	1		see page 486	

¹⁾ IP 65 available on request.

Special voltages available on request. We reserve the right to make technical modifications.

Roof-mounted, useful cooling output 3000 W, water-carrying parts CuAL

Model No. SK	3374.500	3374.100	Page
Thermostat (factory setting +35°C)	e-Comfort controller ■	–	
	Basic controller –	■	
Useful cooling output	L 35 W 10, 400 l/h	3000 W	
Rated operating voltage V, Hz	230, 1~, 50/60		
Dimensions mm	W x H x D 400 x 950 x 140		

Rated current max.	0.57 A/0.78 A
Pre-fuse T	4.0 A
Cooling medium	Water (for specifications see Internet; user manual)
Water inlet temperature	+1°C to +30°C
Water connection	Quick-release fastener system
Permissible operating pressure p. max.	1 to 10 bar
Operating temperature and setting range	+1°C to +70°C
Protection category to IEC 60 529	IP 55 ¹⁾
Duty cycle	100%
Type of connection	Plug-in terminal strip
Weight	20 kg
Air throughput of fan (unimpeded air flow)	700/730 m ³ /h

Accessories	Packs of			
Door-operated switch	1	4127.010	4127.010	684
SK BUS system	1	3124.100	–	477
Interface board	1	3124.200	–	477
Condensate hose	1	3301.612	3301.612	485
Threaded adaptor for quick-release fastener with G3/8" internal thread	2	3201.900	3201.900	486
Threaded adaptor for quick-release fastener with G3/8" external thread	2	3201.910	3201.910	486
Flow regulator valve	1		see page 486	

¹⁾ IP 65 available on request.

Special voltages available on request. We reserve the right to make technical modifications.