

# TopTherm air/air heat exchangers



Climate control accessories Page 369

#### Temperature control:

- Electronic control with digital display (factory setting +35°C)

#### Colour:

- RAL 7035

#### Protection category IP to

#### IEC 60 529:

- Internal circuit IP 54

#### Supply includes:

- Complete unit ready for connection
- Plug-in terminal strip
- Floating fault signal contact in case of overtemperature

#### Approvals:

Available on the Internet

#### Performance diagrams:

Available on the Internet

#### Technical details:

Available on the Internet

## Specific thermal output 17.5 – 90 W/K, wall-mounted with controller

| Model No.   | Packs of | 3126.100       | 3127.100       | 3128.100       | 3129.100       | 3130.100       | Page |
|---|----------|----------------|----------------|----------------|----------------|----------------|------|
| Rated operating voltage V, ~, Hz  |          | 230, 1~, 50/60 | 230, 1~, 50/60 | 230, 1~, 50/60 | 230, 1~, 50/60 | 230, 1~, 50/60 |      |
| <b>Specific thermal output W/K</b>  |          | <b>17.5</b>    | <b>30</b>      | <b>45</b>      | <b>60</b>      | <b>90</b>      |      |
| Max. rated current per fan A  |          | 0.11 / 0.13    | 0.28 / 0.34    | 0.3 / 0.4      | 0.38 / 0.4     | 0.67 / 0.88    |      |
| Pre-fuse A  |          | 2              | 2              | 2              | 2              | 4              |      |
| Output per fan W  |          | 23 / 27        | 60 / 75        | 70 / 90        | 85 / 90        | 150 / 200      |      |
| Air throughput of fans (unimpeded air flow), external circuit m <sup>3</sup> /h |          | 265 / 315      | 480 / 525      | 600 / 625      | 860 / 900      | 850 / 945      |      |
| Air throughput of fans (unimpeded air flow), internal circuit m <sup>3</sup> /h |          | 265 / 315      | 480 / 525      | 600 / 625      | 860 / 900      | 850 / 945      |      |
| Width mm  |          | 280            | 400            | 400            | 400            | 400            |      |
| Height mm   |          | 550            | 950            | 950            | 950            | 1580           |      |
| Depth mm  |          | 150            | 205            | 205            | 225            | 215            |      |
| Operating temperature range   |          | -5°C...+55°C   | -5°C...+55°C   | -5°C...+55°C   | -5°C...+55°C   | -5°C...+55°C   |      |
| Weight kg   |          | 10.0           | 18.0           | 19.0           | 21.0           | 34.0           |      |
| <b>Accessories</b>  |          |                |                |                |                |                |      |
| Filter mats   | 3 pc(s). | 3286.300       | 3286.400       | 3286.400       | 3286.400       | 3286.400       | 369  |
| Metal filters   | 1 pc(s). | 3286.310       | 3286.410       | 3286.410       | 3286.410       | 3286.410       | 370  |