

# TopTherm chillers

## Output class 3000 – 6000 W

Model No.	Packs of	3320.600	3334.600	3334.660	Page
Total cooling output at $T_w = 10^\circ\text{C} / T_u = 32^\circ\text{C}$ kW		2.7 / 3	3.9 / 4.7	4.8 / 5.2	
<b>Total cooling output at <math>T_w = 18^\circ\text{C} / T_u = 32^\circ\text{C}</math> kW</b>		<b>3 / 3.4</b>	<b>4.5 / 5.4</b>	<b>6.1 / 6.6</b>	
Power consumption $P_{el}$ 50/60 Hz kW		2.1 / 2.7	2.9 / 4.1	4.1 / 4.8	
Rated operating voltage V, ~, Hz		400, 3~, 50 460, 3~, 60	400, 3~, 50 460, 3~, 60	400, 3~, 50 460, 3~, 60	
Width mm		602	602	602	
Height mm		676	676	1050	
Depth mm		645	645	645	
Rated current max. A		4.1 / 4.4	5.7 / 6.3	8.4 / 9	
Operating temperature range		+10°C...+43°C	+10°C...+43°C	+10°C...+43°C	
Refrigerant		R134a	R134a	R134a	
Integral tank level display		-	-	■	
Water connection	½" internal thread	■	■	-	
	¾" internal thread	-	-	■	
Temperature hysteresis		+/- 2 K	+/- 2 K	+/- 2 K	
Temperature of liquid		+10°C...+30°C	+10°C...+30°C	+10°C...+30°C	
Design		Open	Open	Open	
Tank		PP plastic	PP plastic	PP plastic	
Tank capacity l		30	30	30	
Weight kg		88.0	94.0	125.0	
<b>Accessories</b>					
Metal filters	1 pc(s).	3286.520	3286.520	3286.510	370



**New**

**LCP –  
Liquid Cooling Package**

see page 429