

### Roof plates

#### for TS

For enclosures without roof plate and in exchange for the standard roof in other TS enclosures.

#### Material:

– Sheet steel, 1.5 mm

#### Surface finish:

– Textured paint

#### Colour:

– RAL 7035

#### Supply includes:

– Assembly parts



#### IP 55, solid

For enclosures		Packs of	Model No.
Width mm	Depth mm		
400	600	1 pc(s).	<b>9671.646</b>
600	600	1 pc(s).	<b>9671.666</b>
800	600	1 pc(s).	<b>9671.686</b>
400	800	1 pc(s).	<b>9671.648</b>
600	800	1 pc(s).	<b>9671.668</b>
800	800	1 pc(s).	<b>9671.688</b>

#### For cable entry glands

For enclosures		Required number of glands	Packs of	Model No.
Width mm	Depth mm			
600	400	2 pc(s).	1 pc(s).	<b>9665.943</b>
850	400	3 pc(s).	1 pc(s).	<b>9665.953</b>
1100	400	4 pc(s).	1 pc(s).	<b>9665.963</b>
400	600	3 pc(s).	1 pc(s).	<b>9671.546</b>
600	600	4 pc(s).	1 pc(s).	<b>9665.903</b>
800	600	8 pc(s).	1 pc(s).	<b>9671.586</b>
850	600	6 pc(s).	1 pc(s).	<b>9665.913</b>
1100	600	8 pc(s).	1 pc(s).	<b>9665.923</b>
400	800	4 pc(s).	1 pc(s).	<b>9671.548</b>
600	800	8 pc(s).	1 pc(s).	<b>9671.568</b>
800	800	8 pc(s).	1 pc(s).	<b>9671.588</b>

#### IP 4X

In order to achieve a protection category of IP 41, a roof plate IP 55 should be fitted above the existing roof plate using four spacers 7967.000.

For enclosures		Packs of	Model No.
Width mm	Depth mm		
400	600	1 pc(s).	<b>9671.364</b>
600	600	1 pc(s).	<b>9671.366</b>
800	600	1 pc(s).	<b>9671.368</b>
400	800	1 pc(s).	<b>9671.384</b>
600	800	1 pc(s).	<b>9671.386</b>
800	800	1 pc(s).	<b>9671.388</b>

#### Also required:

Cable entry gland, see page 584

#### IP 2X with ventilation hole, build height: 72 mm

For enclosures		Packs of	Model No.
Width mm	Depth mm		
400	600	1 pc(s).	<b>9671.846</b>
600	600	1 pc(s).	<b>9660.235</b>
800	600	1 pc(s).	<b>9660.245</b>
1000	600	1 pc(s).	<b>9660.255</b>
1200	600	1 pc(s).	<b>9660.265</b>
400	800	1 pc(s).	<b>9671.848</b>
600	800	1 pc(s).	<b>9659.525</b>
800	800	1 pc(s).	<b>9659.535</b>
1000	800	1 pc(s).	<b>9659.545</b>
1200	800	1 pc(s).	<b>9659.555</b>