

ISV distribution enclosures

Installation modules



Connection terminal blocks

- For connecting copper and aluminium conductors
- Single-wire or multi-wire conductors with crimped wire end ferrule or laminated copper bar

Material:

– Duroplastic

Colour:

– RAL 7035

Design	Connection of round conductors mm ²	Clamping area for laminated copper bars, W x H mm	Packs of	Model No.	Page
250 A, 5-pole	1 x 16 – 150 or 2 x 16 – 70	17 x 21	1 pc(s).	9666.340	
400 A, 5-pole	1 x 50 – 240 or 2 x 25 – 120	25 x 21	1 pc(s).	9666.350	

Also required

Description	Size				Packs of	Model No.	Page
	Width unit		Height unit				
	WU	mm	U	mm			
Mounting kit for connection terminal block	1	250	3	450	1 pc(s).	9666.310	
Contact hazard protection modules	1	250	3	450	1 pc(s).	9666.020	299

Accessories

Laminated copper bars	255
1 WU $\hat{=}$ 250 mm	
1 U $\hat{=}$ 150 mm	



NH fuse-switch disconnecter modules

- Suitable for the accommodation of NH fuse-switch disconnectors for mounting plate assembly
- Cover is prepared for a lead seal

Material:

– Cover: Polystyrene (PS)

Colour:

– RAL 7035

Note:

– Blanking cover 9666.665 should be used to seal unneeded cut-outs for NH fuse-switch disconnectors size 00

To fit NH disconnector		Size				Packs of	Model No.	Page
Size	Model No.	Width unit		Height unit				
		WU	mm	U	mm			
2 pc(s), size 00	9344.000/.010/ .020/.030/.040/.050	1	250	2	300	1 pc(s).	9666.380	
4 pc(s), size 00		2	500	2	300	1 pc(s).	9666.390	
1 pc(s), size 1	9344.100/.110/ 130/.150	1	250	3	450	1 pc(s).	9666.400	
1 pc(s), size 2	9344.200/.210/ 230/.250	1	250	3	450	1 pc(s).	9666.410	
1 pc(s), size 3 or 2 pc(s), size 2	9344.300/.310/ 330/.350	2	500	3	450	1 pc(s).	9666.060 ¹⁾	299
						1 pc(s).	9666.420 ¹⁾	300

1 WU $\hat{=}$ 250 mm
1 U $\hat{=}$ 150 mm

¹⁾ Module unit consisting of disconnector cross-member 9666.420 and contact hazard protection module 9666.060



Disconnector cross-member

for NH fuse-switch disconnecter, size 2/3

- Suitable for the accommodation of NH fuse-switch disconnectors for mounting plate assembly

To fit NH disconnector		Size				Packs of	Model No.	Page
Size	Model No.	Width unit		Height unit				
		WU	mm	U	mm			
1 pc(s), size 3 or 2 pc(s), size 2	9344.300/.310/ 330/.350	2	500	3	450	1 pc(s).	9666.420	

Also required

Contact hazard protection modules	1 pc(s).	9666.060	299
-----------------------------------	----------	----------	-----