

System accessories AX

Assembly components

Metal multi-tooth screw

For the round holes Ø 4.5 mm in the enclosure section, punched rails and punched sections without mounting flanges.

Multi-tooth drive for optimum transmission of torques, an extended tool life and increased safety and reliability when tightening and loosening screw connections.

Type of screw	Dimensions mm	Packs of	ModelNo.
Metal multi-tooth screws	5.5 x 13	300 pc(s).	2486.600
Metal multi-tooth screws for stainless steel	5 x 13	300 pc(s).	2486.400
Self-tapping screws (hex screws)	M5 x 10	500 pc(s).	2504.000
Self-tapping screws	ST 4.8 x 16	300 pc(s).	2487.000



Self-tapping screw

For the round holes Ø 4.5 mm in the enclosure section, punched rails and punched sections without mounting flanges.



Self-tapping screw

Mark, drill and tighten in a single operation using electric or pneumatic tools.

For metal thickness: 0.8 – 3 mm

Length: 16 mm

Usable length: 9.5 mm

Width across flats: 8 mm



Isolator cap

for screw head

To isolate screw heads e.g. within the cable duct.

Material:

- Plastic

Packs of	Model No.
100 pc(s).	8800.770

