

# Doors/locks

## Door variants



### Glazed door

Instead of a sheet steel door or rear panel.

**Material:**

- Frame: Extruded aluminium section
- Viewing window: Single-pane safety glass, 3 mm

**Surface finish:**

- Powder-coated

**Colour:**

- Frame and corner pieces: RAL 7035
- Viewing window (printed mask on the inside): RAL 9005

**Protection category IP to IEC 60 529:**

- IP 55

**Supply includes:**

- Glazed door
- Locking rod with double-bit lock insert
- 180° hinges (4 pc(s).)

For enclosures		Model No.
Width mm	Height mm	
600	1800	<b>8618.000</b>
800	1800	<b>8618.010</b>
600	2000	<b>8618.020</b>
800	2000	<b>8618.030</b>
600	2200	<b>8618.040</b>
800	2200	<b>8618.050</b>



**Also required:**

- When mounting instead of the rear panel or double door: Lock components for frame 8618.110, see page 110



**Accessories:**

- Lock system, see page 120

### Lock components

For retrofitting a glazed door or sheet steel door in place of a rear panel.

**Material:**

- Die-cast zinc

**Supply includes:**

- Assembly parts

P. of	Model No.
4 pc(s).	<b>8618.110</b>

### Lockable and adjacent door

For example, if two 400 mm doors instead of one 800 mm wide door are used to comply with escape routes. May also be fitted instead of an 800 mm wide rear panel.

**Material:**

- Sheet steel

**Surface finish:**

- Dipcoat-primed, powder-coated on the outside

**Colour:**

- RAL 7035

**Protection category IP to IEC 60 529:**

- IP 55

**Supply includes:**

- 2 doors, including tubular door frame, hinges and lock components

For enclosures		Model No.
Width mm	Height mm	
800	2000	<b>8618.120</b>



**Accessories:**

- Lock system, see page 120