

# Distributor racks



482.6 mm (19") installation system Page 678 Monitoring Page 445 Power System Module Page 409 Accessories for Data Rack Page 682

## Material:

- Profile frame, base/plinth: Sheet steel
- Feet: Die-cast zinc

## Colour:

- Profile frame, base/plinth: RAL 7035
- Trim panel, feet: RAL 5018

## Load capacity:

- Max. 150 kg, static/level

## Supply includes:

- Torsionally stiff profile frame with 482.6 mm (19") punchings
- Stable base/plinth with integral feet, with the option of floor anchoring without base trim panels
- Levelling feet
- Assembly parts


## Note:

- Order second mounting level separately

## Technical details:

Available on the Internet

Photo shows a configuration example with equipment not included in the scope of supply



## Data Rack

Units U	Packs of	31	36	40	45	Page
<b>Width (B) mm</b>		550	550	550	550	
<b>Height (H) mm</b>		1499.5	1721.8	1899.5	2121.8	
<b>Depth (T1) mm</b>		750	750	750	750	
Distance from the second mounting level, 50 mm pitch pattern (T2) mm		150 - 350	150 - 350	150 - 350	150 - 350	
<b>Model No.</b>	1 pc(s).	<b>7391.000</b>	<b>7396.000</b>	<b>7400.000</b>	<b>7445.000</b>	
<b>Accessories</b>						
Second pair of mounting angles	1 pc(s).	7296.000	7297.000	7298.000	7299.000	682
Twin castors	1 set(s)	7495.000	7495.000	7495.000	7495.000	522
Component shelf 2 U, static installation		see page	see page	see page	see page	631
Cable duct	1 pc(s).	5502.105	5502.105	5502.105	5502.145	673
Cable routing across the 482.6 mm (19") mounting level	6 pc(s).	7016.100	7016.100	7016.100	7016.100	677
	6 pc(s).	7016.110	7016.110	7016.110	7016.110	677
Slide rails		see page	see page	see page	see page	687
Baying connector	3 pc(s).	7494.000	7494.000	7494.000	7494.000	682
Depth stays	2 pc(s).	7401.000	7401.000	7401.000	7401.000	682
Continuous slide rail	2 pc(s).	7402.000	7402.000	7402.000	7402.000	682
Keyboard drawer 2 U	1 pc(s).	7281.035	7281.035	7281.035	7281.035	712