

Hygienic Design

Accessories



Levelling feet HD

Benefits:

- Minimal cleaning time, due to fully covered, permanently sealed threads
- Compensation of floor inclines up to an angle of 10° thanks to flexible base plate
- Baying is even possible on sloping floors, thanks to a large levelling range of 55 mm

Load capacity:

- Max. 5000 N static per levelling foot

Material:

- Stainless steel 1.4301 (AISI 304)

Supply includes:

- Assembly parts and seals

Thread	Levelling range mm	Base mount	Packs of	Model No.
M12	120 – 175	without	4 pc(s).	4000.200
		with	4 pc(s).	4000.210



Wall spacer bracket HD

Benefits:

- Creates space for cleaning behind the enclosure
- Shorter assembly times by eliminating the need for an all-round seal
- Greater hygiene safety by avoiding an uncontrollable dead space or gap between the enclosure and wall

Functional principle:

- Mounting on the wall optionally from the enclosure interior via a through-hole (max. M8) or from the rear via an integral M10 thread

Material:

- Stainless steel 1.4301 (AISI 3304)

Supply includes:


- Assembly parts and seals

Wall distance mm	Packs of	Model No.
50	1 pc(s).	4000.100

Mounting alternatives:

Attachment from inside

Attachment from outside



Enclosure key HD

Packs of	Model No.
1 pc(s).	2549.600



Bit HD

for universal key 2549.500

See page 573

Packs of	Model No.
1 pc(s).	2549.510



Cam lock HD

Hygienic Design variant for easy, safe cleaning.

Applications:

- Compact enclosures AE stainless steel (except 1017.XXX and 1019.XXX).
- May be integrated into customised applications, e.g. covers of machine panels

Material:

- Stainless steel 1.4404 (AISI 316L)

Packs of	Model No.
1 pc(s).	2304.010

+ **Accessories:**

- Enclosure key HD, see page 172