


# Doors/locks

## Installation accessories for modular front design TS



### Modular front design

#### for baying systems TS 8

(see page 76)

Suitable for 400, 600 and 800 mm wide TS enclosures instead of a door or rear panel.

The partial doors with and without viewing panels including cross members may be combined with one another as required. A trim panel is required at the top and bottom in each case.

The requirements for your individual front design and the considerations which must be taken into account are illustrated on the sample configuration opposite.

- 1 Front trim panel, top
- 2 Front trim panel, bottom
- 3 Partial door with viewing window
- 4 Partial door

#### Protection category IP to IEC 60 529:

- IP 54 for a completed enclosure



### Partial doors

#### for TS

The door may be optionally hinged on the right or left. The partial door is attached to the TS enclosure with no drilling required. In the case of partial doors without a viewing panel (height 600 – 1000 mm), monitor frame 2305.000 may be installed. Standard double-bit lock insert may be exchanged for lock inserts, type F, and from a height of 600 mm, for comfort handles.

#### Material:

- Partial door: Sheet steel, 2 mm
- Viewing window: 3 mm single-pane safety glass

#### Surface finish:

- Textured paint

#### Colour:

- RAL 7035

#### Supply includes:

- Cross member, hinges and lock parts.
- Assembly parts

#### ! Also required:

- Front trim panels, top, see page 553 or Trim panel, hinged at the top, see page 554
- Front trim panels, bottom, see page 553

#### + Accessories:

- Monitor frame 2305.000, see page 558
- Lock inserts, type F, see page 570
- Comfort handle, see page 564
- Perforated mounting strips, see page 553

#### Technical details:

Available on the Internet

#### For enclosure width 400 mm

| Height mm | With viewing window | Packs of | Model No.       |
|-----------|---------------------|----------|-----------------|
| 150       | –                   | 1 pc(s). | <b>9672.141</b> |
| 200       | –                   | 1 pc(s). | <b>9672.142</b> |
| 300       | –                   | 1 pc(s). | <b>9672.143</b> |
| 400       | –                   | 1 pc(s). | <b>9672.144</b> |
| 600       | –                   | 1 pc(s). | <b>9672.146</b> |
| 800       | –                   | 1 pc(s). | <b>9672.148</b> |
| 1000      | –                   | 1 pc(s). | <b>9672.140</b> |
| 1600      | –                   | 1 pc(s). | <b>9672.156</b> |
| 1800      | –                   | 1 pc(s). | <b>9672.158</b> |
| 2000      | –                   | 1 pc(s). | <b>9672.150</b> |

#### For enclosure width 600 mm

| Height mm | With viewing window | Packs of | Model No.       |
|-----------|---------------------|----------|-----------------|
| 150       | –                   | 1 pc(s). | <b>9672.161</b> |
| 200       | –                   | 1 pc(s). | <b>9672.162</b> |
| 300       | –                   | 1 pc(s). | <b>9672.163</b> |
| 400       | –                   | 1 pc(s). | <b>9672.164</b> |
| 600       | –                   | 1 pc(s). | <b>9672.166</b> |
| 600       | ■                   | 1 pc(s). | <b>9672.167</b> |
| 800       | –                   | 1 pc(s). | <b>9672.168</b> |
| 800       | ■                   | 1 pc(s). | <b>9672.169</b> |
| 1000      | –                   | 1 pc(s). | <b>9672.160</b> |
| 1600      | –                   | 1 pc(s). | <b>9672.176</b> |
| 1800      | –                   | 1 pc(s). | <b>9672.178</b> |
| 2000      | –                   | 1 pc(s). | <b>9672.170</b> |

#### For enclosure width 800 mm

| Height mm | With viewing window | Packs of | Model No.       |
|-----------|---------------------|----------|-----------------|
| 150       | –                   | 1 pc(s). | <b>9672.181</b> |
| 200       | –                   | 1 pc(s). | <b>9672.182</b> |
| 300       | –                   | 1 pc(s). | <b>9672.183</b> |
| 400       | –                   | 1 pc(s). | <b>9672.184</b> |
| 600       | –                   | 1 pc(s). | <b>9672.186</b> |
| 600       | ■                   | 1 pc(s). | <b>9672.187</b> |
| 800       | –                   | 1 pc(s). | <b>9672.188</b> |
| 1000      | –                   | 1 pc(s). | <b>9672.180</b> |
| 1600      | –                   | 1 pc(s). | <b>9672.196</b> |
| 1800      | –                   | 1 pc(s). | <b>9672.198</b> |
| 2000      | –                   | 1 pc(s). | <b>9672.190</b> |