

482.6 mm (19") installation system

Slide rails

Slide rails, static installation

for TS-IT

For mounting between 482.6 mm (19") mounting angles.

- System punchings for mounting accessories and cooling active components

Load capacity:

- 30 kg, static

Material:

- Sheet steel


Surface finish:

- Zinc-plated

Supply includes:

- Assembly parts

U	Length mm	Packs of	Model No.
2	150	2 pc(s).	5501.400



Slide rails, static installation

for TS-IT

For mounting between a front and a rear pair of mounting angles.

- To support heavy installed equipment
- Side system punchings for mounting accessories and cooling components that expel to the side
- Simply locate into the system punchings of the TS-IT

Load capacity:

- 80 kg, static

Material:

- Sheet steel

Surface finish:

- Zinc-plated

Supply includes:

- Assembly parts

Note:

- Effective contact surface 35 mm per side

U	482.6 mm (19") distance between levels mm	Packs of	Model No.
1	345	2 pc(s).	5501.410
1	445	2 pc(s).	5501.420
1	545	2 pc(s).	5501.430
1	645	2 pc(s).	5501.440
1	745	2 pc(s).	5501.450



Depth-variable slide rails

482.6 mm (19")

for TS-IT

For mounting between a front and a rear pair of mounting angles. Thanks to side attachment on the front section, all three mounting holes in the EIA system punchings remain available for screw-fastening the equipment.

- To support heavy installed equipment
- To adapt to individual distances between levels
- Tool-free, time-saving one-man assembly from the enclosure front
- All three mounting holes in the EIA system punchings are available for screw-fastening the equipment
- Alternatively, direct attachment to the 482.6 mm (19") system punchings is also possible

482.6 mm (19") distance between levels mm	Load capacity kg	Packs of	Model No.
400 - 600	80	2 pc(s).	5501.460
600 - 900	150	2 pc(s).	5501.480

Material:

- Sheet steel

Surface finish:

- Zinc-plated

Supply includes:

- Assembly parts

Note:

- Effective contact surface 25 mm per side

