


# Interior installation

## Rail systems



### TS punched section with mounting flange, 17 x 73 mm

Variable, with 5 rows of holes for universal skeleton structures or partial assembly. Simply locate into the TS punchings and secure.

#### Installation options:

- On the vertical TS enclosure section
  - On the outer mounting level, all-round, at the same height
  - On the inner mounting level, all-round, height-offset
- In the tubular door frame for TS, SE and PC
- For SE, may additionally be mounted on the top horizontal section in the depth
- In CM and TP via rail for interior installation
  - In the depth, for outer mounting level
  - In the width, for inner mounting level

#### Material:

- Sheet steel

#### Surface finish:

- Zinc-plated

#### Supply includes:

- Assembly screws



#### Also required:

- For installation in CM, TP:  
Rail for interior installation, see page 605



#### Accessories:

- Screws, see page 625
- Cable tie for fast assembly 2597.000, see page 667

#### For the outer mounting level

For enclosure width/depth mm	Packs of	Model No.
300	4 pc(s).	<b>8612.130</b>
400	4 pc(s).	<b>8612.140</b>
500	4 pc(s).	<b>8612.150</b>
600	4 pc(s).	<b>8612.160</b>
800	4 pc(s).	<b>8612.180</b>
1000	4 pc(s).	<b>8612.100</b>
1200	4 pc(s).	<b>8612.120</b>

#### For the inner mounting level or for tubular door frames

For door width (for tubular door frame) mm	For enclosure width/depth (for inner mounting level) mm	Length mm	Packs of	Model No.
400	300	290	4 pc(s).	<b>8612.030</b>
500	400	390	4 pc(s).	<b>8612.040</b>
600	500	490	4 pc(s).	<b>8612.050</b>
–	600	590	4 pc(s).	<b>8612.060</b>
800	–	690	4 pc(s).	<b>8612.070</b>
900	800	790	4 pc(s).	<b>8612.080</b>
1000	–	890	4 pc(s).	<b>8612.090</b>
–	1000	990	4 pc(s).	<b>8612.000</b>
–	1200	1190	4 pc(s).	<b>8612.020</b>

#### Configuration examples:

See from page 598



### Attachment TS

for TS punched section with mounting flange, 17 x 73 mm

#### Benefits:

- For attaching the TS punched section with mounting flange where access to installed equipment, such as mounting plates, is blocked by the screw fastening
- May also be screw-fastened onto the punched section with mounting flange or enclosure frame and used as a support for contact hazard protection covers or master switch trim panels

Packs of	Model No.
12 pc(s).	<b>8612.010</b>

#### Material:

- Sheet steel

#### Surface finish:

- Zinc-plated