

Baying enclosure system VX25, stainless steel



System accessories Page 78 Cable entry Page 182

Material and surface finish:

- Enclosure frame: Stainless steel 1.4301 (AISI 304), 1.5 mm
- Roof: Stainless steel 1.4301 (AISI 304), 1.5 mm, exterior brushed, grain size 400
- Door: Stainless steel 1.4301 (AISI 304), 2 mm, exterior brushed, grain size 400
- Rear panel: Stainless steel 1.4301 (AISI 304), 1.5 mm, exterior brushed, grain size 400
- Gland plate: Stainless steel 1.4301 (AISI 304), 1.5 mm
- Mounting plate: Sheet steel, 3 mm, zinc-plated

Supply includes:


- Enclosure frame
- Door(s) (r/h hinge, may be swapped to opposite side)
- Roof
- Gland plate
- Rear panel
- Mounting plate
- Lock: 3 mm double-bit
- 2 punched rails 18 x 39 mm

Note:

- Due to the hardness of the material, we recommend using metal multi-tooth screw 2486.400 for the interior installation.

Approvals:

- UL
- cUL



Protection category IP to IEC 60 529:

- IP 66

NEMA protection category:

- NEMA 4X

IP 66/NEMA 4X

Width (B) mm	P. of	800	Page
Height (H) mm		2000	
Depth (T) mm		600	
Mounting plate width (F) mm		699	
Mounting plate height (G) mm		1896	
Model No.	1 pc(s).	8458.000	
Weight, approx. kg		128.9	
Accessories			
Base/plinth corner pieces with base/plinth trim panel, front and rear, 100 mm	2 pc(s).	8620.051	87
Base/plinth trim panels, sides, 100 mm	2 pc(s).	8620.070	88
Base/plinth corner pieces with base/plinth trim panel, front and rear, 200 mm	2 pc(s).	8620.061	87
Base/plinth trim panels, sides, 200 mm	2 pc(s).	8620.080	88
Punched section with mounting flange 23 x 89 mm, stainless steel, in the depth	4 pc(s).	8100.732	151
Side panels, screw-fastened, stainless steel	2 pc(s).	8700.050	96
Baying bracket, internal	6 pc(s).	8617.500	106
Baying block, internal	6 pc(s).	8617.501	106
Comfort handle VX for lock inserts	1 pc(s).	8618.220	120
Comfort handle VX for semi-cylinder	1 pc(s).	8618.280	120
Lock inserts		see page	121
Wiring plan pocket, sheet steel, depth 35 mm	1 pc(s).	4118.500	127
Wiring plan pocket, sheet steel, depth 90 mm	1 pc(s).	4118.000	127
LED system light		see page	163
Cable duct		see page	186
Cable clamp rail, right angle section	2 pc(s).	8619.420	187