

# Baying systems TS 8



System accessories Page 507 Cable entry Page 650

## Material and surface finish:

- Enclosure frame: Sheet steel, 1.5 mm, dipcoat-primed and powder-coated, textured paint
- Roof: Sheet steel, 1.5 mm, dipcoat-primed and powder-coated, textured paint
- Door: Sheet steel, 2 mm, dipcoat-primed and powder-coated, textured paint
- Rear panel: Sheet steel, 1.5 mm, dipcoat-primed and powder-coated, textured paint

- Base: Sheet steel, 1.5 mm, dipcoat-primed, powder-coated on the outside, textured paint
- Mounting plate: Sheet steel, 3 mm, zinc-plated

## Colour:

- RAL 7035

## Protection category IP to IEC 60 529:

- IP 66

## Protection category NEMA:


- NEMA 4

## Supply includes:

- Enclosure frame with door
- Roof plate
- Base, solid
- Rear panel
- Mounting plate
- 4 eyebolts
- Lock: 3 mm double-bit

## Approvals:

- UL
- cUL



## IP 66/NEMA 4

Width (B) mm	Packs of	800	Page
Height (H) mm		2000	
Depth (T) mm		600	
Mounting plate width (F) mm		699	
Mounting plate height (G) mm		1896	
<b>Model No.</b>	1 pc(s).	<b>8806.580</b>	
<b>Accessories</b>			
Side panels, screw-fastened, sheet steel	2 pc(s).	8106.235	534
Quick-fit baying clamp, one-piece	6 pc(s).	8800.500	543
Baying clamp, horizontal	4 pc(s).	8800.400	543
Baying frame IP 66/NEMA 4, NEMA 4X	1 pc(s).	8700.010	535
Angular baying bracket	4 pc(s).	8800.430	545
Base/plinth components, front and rear, 100 mm	1 set(s)	8601.800	513
Base/plinth trim panels, side, 100 mm	1 set(s)	8601.060	514
Base/plinth components, front and rear, 200 mm	1 set(s)	8602.800	513
Base/plinth trim panels, side, 200 mm	1 set(s)	8602.060	514
Cable clamp rails	2 pc(s).	4192.000	665
Rail systems		from page	605
Sheet steel wiring plan pockets	1 pc(s).	4118.000	578
Cable duct		see page	664
System lights		from page	634
Lock systems		from page	561