

TopTherm wall-mounted cooling units "Blue e"

Output class 2500 W

Model No.		Packs of	3329.500	3329.510	3329.540	3329.600	3329.640	Page
Material	Sheet steel		■	■	■	–	–	
	Stainless steel		–	–	–	■	■	
Colour	RAL 7035		■	■	■	–	–	
Total cooling output 50 Hz L35 L35 to DIN EN 14511 kW			2.55	2.55	2.55	2.55	2.55	
Total cooling output 50/60 Hz L35 L35 kW			2.55 / 2.71	2.55 / 2.71	2.55 / 2.75	2.55 / 2.71	2.55 / 2.75	
Total cooling output 50/60 Hz L35 L50 kW			1.89 / 1.97	1.89 / 1.97	1.95 / 2	1.89 / 1.97	1.95 / 2	
Rated operating voltage V, ~, Hz			230, 1~, 50/60	115, 1~, 50/60	400, 3~, 50 460, 3~, 60	230, 1~, 50/60	400, 3~, 50 460, 3~, 60	
Width (B) mm			400	400	400	400	400	
Height (H) mm			1580	1580	1580	1580	1580	
Depth (T) mm			295	295	295	295	295	
Rated current max. A			8.2 / 9.3	17 / 22	3.7 / 3.8	8.2 / 9.3	3.7 / 3.8	
Start-up current A			20 / 24	44 / 42	6.8 / 7.6	20 / 24	6.8 / 7.6	
Pre-fuse A			16	–	–	16	–	
Transformer circuit-breaker A			–	18...25	–	–	–	
Motor circuit-breaker A			–	–	6.3...10	–	6.3...10	
Power consumption P _{el} 50/60 Hz L35 L35 kW			1.21 / 1.35	1.21 / 1.35	1.2 / 1.4	1.21 / 1.35	1.2 / 1.4	
Power consumption P _{el} 50/60 Hz L35 L50 kW			1.41 / 1.64	1.41 / 1.64	1.45 / 1.75	1.41 / 1.64	1.45 / 1.75	
Operating temperature range			+10°C...+55°C	+10°C...+55°C	+10°C...+55°C	+10°C...+55°C	+10°C...+55°C	
Setting range			+20°C...+55°C	+20°C...+55°C	+20°C...+55°C	+20°C...+55°C	+20°C...+55°C	
Energy efficiency ratio (EER) 50 Hz L35 L35 to DIN EN 14511			2.11	2.11	2.11	2.11	2.11	
Refrigerant g			R134a, 950	R134a, 950	R134a, 950	R134a, 950	R134a, 950	
Permissible operating pressure (p. max.) bar			28	28	28	28	28	
Air throughput of fans (unimpeded air flow), internal circuit / external circuit m ³ /h			1230 / 1230	1230 / 1230	1200 / 1200	1230 / 1230	1200 / 1200	
Weight kg			69.0	76.0	70.0	69.0	70.0	

Accessories

Filter mats	3 pc(s).	3286.400	3286.400	3286.400	3286.400	3286.400	369
Metal filters	1 pc(s).	3286.410	3286.410	3286.410	3286.410	3286.410	370
Door-operated switch	1 pc(s).	4127.010	4127.010	4127.010	4127.010	4127.010	639

Output class 4000 W

Model No.		Packs of	3332.540	3332.640	Page
Material	Sheet steel		■	–	
	Stainless steel		–	■	
Colour	RAL 7035		■	–	
Total cooling output 50 Hz L35 L35 to DIN EN 14511 kW			3.95	3.95	
Total cooling output 50/60 Hz L35 L35 kW			3.95 / 4.35	3.95 / 4.35	
Total cooling output 50/60 Hz L35 L50 kW			3.02 / 3.52	3.02 / 3.52	
Rated operating voltage V, ~, Hz			400, 3~, 50 460, 3~, 60	400, 3~, 50 460, 3~, 60	
Width (B) mm			500	500	
Height (H) mm			1580	1580	
Depth (T) mm			340	340	
Rated current max. A			4.2 / 4.2	4.2 / 4.2	
Start-up current A			9.2 / 11	9.2 / 11	
Pre-fuse			–	–	
Transformer circuit-breaker			–	–	
Motor circuit-breaker A			6.3...10	6.3...10	
Power consumption P _{el} 50/60 Hz L35 L35 kW			1.6 / 2	1.6 / 2	
Power consumption P _{el} 50/60 Hz L35 L50 kW			1.87 / 2.34	1.87 / 2.34	
Operating temperature range			+10°C...+55°C	+10°C...+55°C	
Setting range			+20°C...+55°C	+20°C...+55°C	
Energy efficiency ratio (EER) 50 Hz L35 L35 to DIN EN 14511			2.47	2.47	
Refrigerant g			R134a, 2995	R134a, 2995	
Permissible operating pressure (p. max.) bar			28	28	
Air throughput of fans (unimpeded air flow), internal circuit / external circuit m ³ /h			1500 / 2000	1500 / 2000	
Weight kg			91.0	91.0	

Accessories

Filter mats	3 pc(s).	3286.400	3286.400	3286.400	369
Metal filters	1 pc(s).	3286.410	3286.410	3286.410	370
Door-operated switch	1 pc(s).	4127.010	4127.010	4127.010	639