

Mini-PLS fuse elements



Busbar system Page 270 Busbar connection adaptor Page 270 Component adaptor Page 272/273

Bus-mounting fuse base

Material:

- Polyamide (PA 6.6).
- Fire protection corresponding to UL 94-V0

Colour:

- Chassis: RAL 9011
- Cover: RAL 7035

NH fuse-switch disconnectors

Material:

- Fibreglass-reinforced polyamide
- Fire protection corresponding to UL 94-V0
- Contact tracks: Silver-plated hard copper

Colour:

RAL 7035

Basis of test:

- IEC 60 947-3
- IEC 60 269-2 (fuse inserts)

Busbar adaptor

Material:

- Polyamide (PA 6.6).
- Fire protection corresponding to UL 94-V0

Colour:

RAL 9011


Technical information:

Available on the Internet.

Detailed drawings:

Available on the Internet.

Mini-PLS bus-mounting fuse bases (3-pole)




Fuse insert	Packs of	D 02-E18
Rated current		63 A
Rated operating voltage		400 V~
Connection of round conductors ¹⁾ mm ²		1.5 – 16
Width mm		38
Height mm		160
Model No. SV	1	9630.000

Accessories

Identification labels	100	9320.080
-----------------------	-----	----------

¹⁾ Wire end ferrules should be used with fine wire conductors.

NH fuse-switch disconnectors, size 000 (3-pole)



Rated operating current	Packs of	100 A	Page
Rated operating voltage		690 V~	
Cable outlet		top/bottom	
Type of connection		Terminal	
Connection of round conductors mm ²		1.5 – 50	
Clamping area for laminated copper bars W x H mm		10 x 10	
Width mm		89	
Height mm		141.5	
Model No. SV	1	3431.000	296

Also required

Mini-PLS busbar adaptors (3-pole)

With connection cables mm ²		35	
Width mm		90	
Height mm		160	
Model No. SV	1	9629.100	

Accessories

Micro-switch	5	3071.000	324
--------------	---	----------	-----