

Air/air heat exchangers



Climate control accessories Page 369 Therm software Page 385

Colour:

- RAL 7035
- RAL 9005

Protection category IP to IEC 60 529:

- Internal circuit IP 54

Supply includes:

- Complete unit ready for connection
- The fans are connected via two 3-wire connection cables, with wire end ferrules

Note:

- For precise temperature control inside the enclosure, we recommend the enclosure internal thermostat, the digital enclosure internal temperature display and thermostat or the speed control

Technical details:

Available on the Internet

Specific thermal output 66 W/K, roof-mounted

Model No.	Packs of	3248.000	Page
Rated operating voltage V, ~, Hz		230, 1~, 50/60	
Specific thermal output W/K		66	
No. of fans		2	
Max. rated current per fan A		0.45 / 0.55	
Pre-fuse A		4	
Output per fan W		75	
Air throughput of fans (unimpeded air flow), external circuit m ³ /h		965	
Air throughput of fans (unimpeded air flow), internal circuit m ³ /h		965	
Width mm		595	
Height mm		362	
Depth mm		440	
Operating temperature range		-5°C...+55°C	
Type of electrical connection		Connection cable	
Weight kg		16.8	
Accessories			
Digital enclosure internal temperature display and thermostat	1 pc(s).	3114.200	379
Enclosure internal thermostat	1 pc(s).	3110.000	379
Hygrostat	1 pc(s).	3118.000	380
Speed control	1 pc(s).	3120.200	381